

Goulds Centrifugal Pump

Mfg: Goulds

Model:

Stock No: CHDM01B

Serial No:

Goulds Centrifugal Pump. EG&G mechanical seals with water flush. Design pressure 175 psig 100 degrees F. General electric motor, 75 hp, 1785 rpm, 460 V, 87.4 amps, 60 Hz, 3 phase. General electric winding heater: HTR LDS H 120V – 100 W. Inlets: (1) 10 in. dia. flange port, (1) 1 in dia. pipe (water). Outlet: (1) 8 in. dia. flange port. Overall dimensions: 5 ft. 8 in. L x 2 ft. 9 in. W x 2 ft. 7 in. H.



