

Fristam Pump, Model FPX722-145

Mfg: Fristam

Model: FPX722-145.

Stock No. DBBP2611.2

Serial No. 22173480

Fristam Centrifugal Pump. Model: FPX722-145. S/N: 22173480. Capacity: 113 gpm @ 48 psi and 114 tdh. Single mechanical seals. Baldor Industrial Motor, 7-1/2 hp, 3450 rpm, 208-230/460 V, 21-18.8/9.4 amps, 60 Hz, 3 phase. The FPX Series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations. Inlet: 2 in. 'S' line. Outlet: 1-1/2 in. 'S' line. Overall dimensions: 26 in. L x 14 in. W x 15 in. H.



