

Fristam FKL-50 Positive Displacement Pump - 5 HP

Mfg: Fristam

Model: FKL50

Stock No.: CAGC1056

Serial No.: 007720

Fristam rotary lobe positive displacement pump. Model FKL-50. serial 007720. Max pressure: 300 PSI. Displacement per revolution: 0.097 gallons. Max flowrate: 58.2 gallons per minute at 600 RPM. GE Motor: 5 HP, 1745 RPM, 208-230/460V, 60 Hz, 3-phase, 184TCY frame. Nord gear reduction drive: 10.89 ratio. Final RPM: 160 (15.5 GPM). Stainless steel base. Ports: 3 in. clamp. (ACN80)



