

Fristam Centrifugal Pump

Mfg: Fristam

Model: FPX722-145

Stock No. DBBP2624.2

Serial No. 22174060

Fristam Centrifugal Pump. Model: FPX722-145. S/N: 22174060. Capacity: 66 gpm @ 58 psi and 136 tdh. Single mechanical seals. Baldor Industrial Motor, 5 hp, 3450 rpm, 208-230/460 V, 15.2-12/6 amps, 60 Hz, 3 phase. The FPX Series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations. Inlet: 2 in. 'S' line. Outlet: 1-1/2 in. 'S' line. Overall dimensions: 25 in. L x 10 in. W x 10 in. H.



