

Tubar Barrel Dumper

Mfg:

Model:

Stock No. CCFP301.

Serial No.:

Tubar Barrel Dumper.

Tubar Barrel Dumper. Designed with hydraulic lift to raise standard 55 gallon drum to about 5 ft., then tilts to dump load. Sensor height at 77 in. Baldor motor, 1.5 hp, 1725 rpm, 208-220/460 V, 4.2/2.1 amps, 60 Hz, 3 phase. Parker Directional Control Valve, Model: D3W18Y14, 120/110 V, 60/50 Hz, 3000 max psi. Maximum working height is 122 in. Overall dimensions: 91 in. L x 36 in. W. x 84 in. H.

