

## Bell & Gossett 60 Pump

Mfg: Bell & Gossett

Model: 60

Stock No. DBHK010.

Serial No.

Bell & Gossett 60 Pump. Marathon Electric motor,  $\frac{3}{4}$  -  $\frac{1}{2}$  hp, 1725 - 1425 rpm, 208-230/460 - 190/380 V, 2.9-3/1.5 - 2.8/1.4 FLA, 60 - 50 Hz. Pump capacity: 0.5 gpm at 43 ft. head. Flange: 4-3/4 in. diameter with (2) holes, center to center: 3-1/2 in. Inlet/outlet: (2) 2 in. Overall dimensions: 23 in. L x 15 in. W x 10 in. H.

