

SMB Stainless Steel Cooling Tunnel

Mfg: SMB

Model: 04.1.0.213

Stock No. CSWB352.40

Serial No. 3325

SMB Stainless Steel Cooling Tunnel. Model: 04.1.0.213. S/N: 3325. Maximum aperture/clearance above belt per section: 6 ft. 5 in. W x 9 in. H. Conveyor infeed maximum aperture/clearance: 1 ft. 3 in. W x 12 in. H. Conveyor infeed/exit height: 40 in. (14) 11-1/2 in. W x 6 in. H pan access ports. Sew-Eurodrive Motor (infeed conveyor), 4 hp (3 kW), 1700 rpm, 330/575 V, 7.9/4.55 amps, 60 Hz, 3 phase. Sew-Eurodrive Variable Speed Drive. Sew-Eurodrive Motor (infeed conveyor), 4 hp (3 kW), 1700 rpm, 330/575 V, 7.9/4.55 amps, 60 Hz, 3 phase. Sew-Eurodrive Variable Speed Drive, 9.1 rpm (min), 45.6 rpm (max). SMB Stainless Steel Control Panel, includes toggle switches for: pump controls, conveyor controls, run controls. SMB Centrifugal Pumps. ASEA Motors, 2.0 hp, 1730 rpm, 575 V, 2.5 amps, 60 Hz, 3 phase. (2) Fischbach Compact Fan Blowers. Brook Compton and Teco Electric Motors, 5 hp, 1740 and 1750 rpm, 575 V, 5.4 and 5.04 amps, 60 Hz, 3 phase. Danfoss Magflo Flowmeter Transmitter, Type: MAG2500, Code No: 083F3070, power supply: 115/230 VAC, 50/60 Hz. Inlets: (1) 1-1/2 in. dia. media port, (1) 2 in. dia. NPT (media), (1) 2 in. dia. flanged port (media), (1) 2-1/2 in. dia. FNPT (media), (1) 3 in. dia. port (cooling media). Outlets: (1) 1 in. dia. NPT (condensate), (1) 3 in. dia. discharge port (media). Overall dimensions: 67 ft. 3 in. L x 19 ft. 2 in. W x 7 ft. 1 in. H.

Note: the following pictures show the exact unit prior to removal.





These pictures show the unit removed at our facility in Edinburg, TX



















