

Rotary Fryer Filter Unit - 28 in. dia.

Mfg:

Model:

Stock No: DBPF2087.1

Serial No:

Rotary Fryer Filter Unit - 28 in. dia. Drum dimensions: 28 in. dia. x 14 in. W. Sump tank dimensions: 30-1/2 in. L x 16-1/2 in. W x 17 in. H. Maximum oil capacity: 35 gal. Baldor Motor, 1/2 hp, 1725 rpm, 230/460 V, 4.5/1.8 amps, 60 Hz, 3 phase. Motordrive. Hydraulic Torqmotor. Inlets: (1) 1-1/2 in. dia. FNPT, (2) 2 in. dia. ports. Outlets: (1) 1-1/2 in. dia. I-line fitting, (1) 4 in. dia. S-line fitting, (1) 6 in. W x 3 in. H discharge. Overall dimensions: 59 in. L x 58 in. W x 62 in. H.

