

Indeco Electric Duct Heater

Mfg: Indeco



Model: TFZU

Stock No.: DLEC086.a

Serial No.: 1E04 79524

Indeco Electric Duct Heater. Type: TFZU. DWG No. L931N1: c19159-A-0. Control Panel. Catalog No. 103-A3-480-20I. S/N: 1E04 79524. Panel power supply: 480 V, 20 amps, 3 phase. No. of Coils: 6. No. of steps: 1. Coil dimensions: 1 in. dia. x 1 ft. 4 in. L. Heater power supply: 11 hp, 480 V, 60 Hz, 3 phase. Inlets/outlets: 1 ft. 6 in. L x 1 ft. W. (duct). Overall dimensions: 2 ft. 5 in. L x 1 ft. 2 in. W x 3 ft. 2-1/2 in. H.





ELECTRIC DUCT HEATER

INDEECO
ST. LOUIS, MISSOURI

INDEECO CATALOG NUMBER: 19H3

CONTROL CIRCUIT POWER: 240V 50/60 HZ 10A

CUSTOMER FURNISHED INFORMATION: RHC-9402.5

MODEL NUMBER: 19H3

MOUNT WITH ARROW UP

AIRFLOW DIRECTION

WARNING
 * RISK OF ELECTRIC SHOCK. CAN CAUSE INJURY OR DEATH. DISCONNECT ALL REMOTE ELECTRIC POWER SUPPLIES BEFORE SERVICING.

DEATH: DISCONNECT ALL REMOTE ELECTRIC POWER SUPPLIES BEFORE SERVICING.

TIGHTEN ALL ELECTRICAL CONNECTIONS AFTER STARTING.
 SEE WIRING DIAGRAM INSIDE COVER FOR REQUIRED SUPPLY CONDUCTORS, COPPER CONDUCTORS WITH INSULATION RATED 75 DEG. C. MINIMUM.
 AIRFLOW THROUGH HEATER MUST BE FREE OF COMBUSTIBLE PARTICLES, FLAMMABLE VAPORS AND GASES.
 HEATER TERMINAL BOX MUST NOT BE ENCLOSED.
 SEE INSTALLATION INSTRUCTIONS FOR SPACE BETWEEN UNITS, MAXIMUM INLET AIR TEMPERATURE, MINIMUM AIR FLOW ETC.
 HEATER RATED FOR 50 OR 60 HZ A.C. CURRENT.
 SLIP AND DRIVE CONNECTIONS MANUFACTURED UNDER PATENT NO. 4803247

SPECIAL INFORMATION
 ITEM NUMBER: 201-153306 ; ORDER NUMBER: C053394-8
 THIS HEATER IS NOT UL LISTED FOR OUTDOOR USE.

LISTED DUCT HEATER
 NO. 19H3
 WITH INTEGRAL LIMIT CONTROL

INDUSTRIAL ENGINEERING & EQUIPMENT CO.
 425 HANLEY INDUSTRIAL COURT ST. LOUIS, MO 63144 OFFICE: 314/644-4300 FAX: 314/644-5332
 1015448

CONTROL CIRCUIT POWER: 240V 50/60 HZ 10A

SPECIAL FEATURE CODE: 19H3-9402.5

CUSTOMER FURNISHED INFORMATION: RHC-9402.5

MODEL NUMBER: 19H3

MOUNT WITH ARROW UP

AIRFLOW DIRECTION

WARNING
 * RISK OF ELECTRIC SHOCK. CAN CAUSE INJURY OR DEATH. DISCONNECT ALL REMOTE ELECTRIC POWER SUPPLIES BEFORE SERVICING.

TIGHTEN ALL ELECTRICAL CONNECTIONS AFTER STARTING.
 SEE WIRING DIAGRAM INSIDE COVER FOR REQUIRED SUPPLY CONDUCTORS, USE COPPER CONDUCTORS WITH INSULATION RATED 75 DEG. C. MINIMUM.
 AIRFLOW THROUGH HEATER MUST BE FREE OF COMBUSTIBLE PARTICLES, FLAMMABLE VAPORS AND GASES.
 HEATER TERMINAL BOX MUST NOT BE ENCLOSED.
 SEE INSTALLATION INSTRUCTIONS FOR SPACE BETWEEN UNITS, MAXIMUM INLET AIR TEMPERATURE, MINIMUM AIR FLOW ETC.
 HEATER RATED FOR 50 OR 60 HZ A.C. CURRENT.
 SLIP AND DRIVE CONNECTIONS MANUFACTURED UNDER PATENT NO. 4803247