

APV Crepaco Liquiverter High Speed Mixer/Blender- 100 Gallon

Mfg: APV Crepaco

Model:

Stock No. DCBJ654.23

Serial No.:

APV Crepaco Liquiverter High Speed Mixer/Blender- 100 Gallon. 316 stainless steel contact surfaces. 10 in. dia. cup-style impeller. Hinged lid. U.S. Motor, 3 hp, 1750 rpm, 1458 rpm (final), 230/460 V, 8.8/4.4 amps, 60 Hz, 3 phase. The Liquiverter is designed to incorporate dry solids, semi-solids or liquids into a slurry or liquid product. This can also be used to blend, disperse, reconstitute, dissolve, rehydrate, prebreak or rerun soluble solids, soluble pastes and liquids quickly and completely. Inlets: 24 in. L x 24 in. W infeed. Tank discharge: 2-1/2 in. threaded (male). Overall dimensions: 45 in. L x 34 in. W x 67 in. H.

Products typically processed are: candies, chocolate syrup, coffee whiteners, icings, jellies, preserves, marmalades, pie fillings, reconstituted/powdered milk and mixes, salad dressings, sauces, gravies, yeast and nutrient slurries, ice cream rerun, and starch slurry.



