

Fristam Stainless Steel Centrifugal Pump

Mfg: Fristam

Model: FPX3551 65068

Stock No. DCBJ666.4a

Serial No. [\[Link\]](#)

Fristam Stainless Steel Centrifugal Pump. Model: FPX3551 65068. Pump capacity: 295.71 gpm at 42 psi. Product viscosity up to 600 cps, process temperature up to 400°F, maximum inlet pressure: 150 psi, single seal only, internal seal product flush. Impeller dimensions: 9-1/2 in. diameter. Baldor Industrial Motor, 10 hp, 1725 rpm, 208-230/460 V, 28-26/13 amps, 60 Hz, 3 phase. Typical applications: bottling, cleaning applications/CIP, de-alcoholization, distillation, emulsifying, evaporation, mechanical, separation, reverse osmosis, in-line mixing, water conditioning, transfer filtration, extraction, dosing, dialysis, de-gassing, carbonizing, homogenizing, fermentation. Pump inlet: 3 in. $\text{\textcircled{S}}$ qline fitting. Outlet: 2-1/2 in. $\text{\textcircled{S}}$ qline fitting. Overall dimensions: 29 in. L x 14 in. W x 16 in. H.



