

Cintex Metal Detector

Mfg: Cintex

Model:

Stock No.: DNBA012

Serial No.:

Cintex Metal Detector. Model (conveyor): CS2060. S/N (conveyor): 42272. Belt width: 1 ft. Maximum aperture/clearance above belt: 1 ft. 2 in. W x 9-1/2 in. H. Sensitivity tested with test strips as 2.5 mm ferrous metals, 3.0 mm non-ferrous metals, 2.5 non-magnetic stainless steel. Actual numbers vary depending on local site conditions, product tested, and other factors. Power supply: 120 V. Leeson Electric Motor, 1/3 hp, 1725 rpm, 208-230/460 V, 1.6-2/0.8-1 amps, 50/60 Hz, 3 phase. Grove Gear Speed Reducer, ratio: 1.5, rpm out: 1150 (final). Conveyor infeed/exit height: 2 ft. 7 in. H. Overall dimensions: 5 ft. 9 in. L x 3 ft. 4 in. W x 3 ft. 7 in. H.



