

Lord Label Systems Labeler

Mfg: Lord Label Systems

Model: System 1

Stock No.: DNBA075

Serial No.:

Lord Label Systems Labeler. Model: System 1. Estimated capacity: 60 tags per minute based on a 4 x 6 in. label with a 10 in. stroke. Roller dimensions: 3 in. dia. (core) x 7 in. H. Labeler head Height can be adjusted on a scale from 0 to 36 in. Air ratings: vacuum 20-25 psig, air assist: 25-30 psi, tamp/blow 40-45 psi. Air requirements: 80 to 125 psi at 1.5 to 2 cfm. Electrical requirements: 115 VAC. Single-chip microprocessor-based control system with LCD readout provides single-point control. This unit applies pressure sensitive labels onto stationary or moving products in a low to high volume production facility. Overall dimensions: 3 ft. 11 in. L x 3 ft. 10 in. W x 7 ft. 2 in. H.(ACN104a).



