

## Cherry-Burrell Scraped Surface Heat Exchanger- 6 x 72

Mfg: Cherry-Burrell

Model:

Stock No. DFPC435.37

Serial No. A4663

Cherry-Burrell Scraped Surface Heat Exchanger- 6 x 72. S/N: A4663. 3A, ASME, and PED Certified. Contact surface area: 9 ft. sq. Shell MAWP: 400 psi @ 375 °F. Shell MDMT: -20 °F @ 400 psi. Jacket MAWP: 150 psi @ 375 °F. Jacket MDMT: -20 °F @ 150 psi. (24) 6 in. W x 2 in. H scraper blades. Baldor Super E Motor, 20 hp, 1725 rpm, 230/460 V, 48/24 amps, 3 phase, 60 Hz. Typical applications are heating and cooling cheese sauce, pudding, caramel, deboned meat, pet food, and fruit products. Inlets: (1) 2-1/2 in. dia port (ammonia), (1) 1-1/2 in. dia port. Outlets: (2) 1 in. dia. Acme pressure relief ports, (1) 2-1/2 in dia S-Line port, (1) 1/2 in. outlet dia port. Overall dimensions: 12 ft. L x 33 in. W x 20 in. H.



