

2003 Frick/York Refrigeration 3-Fan Evaporator - 8.56 Tons


Mfg: Frick/York

Model: DC25-384

Stock No: DPFI674.a

Serial No: 369660100

2003 Frick/York Refrigeration 3-Fan Evaporator. Model: DC25-384. S/N: 369660100. Refrigerant: R-717 (ammonia). Nominal capacity: 8.56 tons with a 10°F TD, liquid recirculation and a wet coil. Airflow: 12,897 cfm. Design pressure: 230 psig. Coil volume: 3.85 cu. ft. Nominal fin spacing: 5 fins/in. Number of coil rows: 8. Total surface area: 2,494 sq. ft. (3) 24 in. dia. fans. (3) Fan motors, 3/4 hp, 1140 rpm, 230 V, 1.4 FLA, 60 hz, 3 phase. Ceiling-mounted. Galvanized steel construction. The DC line incorporates two vertical coils mounted parallel to each other with a common fan section between the coils. The two-coil design allows for maximum capacity with energy efficient propeller fans in a low profile design. They can be specified as either two-directional horizontal air flow or single direction vertical down air flow. Inlet: (1) 2 in. dia. port. Outlets: (1) 1 in. dia. port. (2) 1-1/2 in. drain. Approximate weight: 2,787 lbs. Overall dimensions: 9 ft. L x 7 ft. 1 in. W x 2 ft. 8 in. H.(ACN150)(BI).





YORK® Refrigeration
YORK INTERNATIONAL

MODEL DC25-384		SERIAL NO. 369660100		MFG DATE 7-8-03	
MOTOR NAMEPLATE DATA					
QTY 3	HP 3/4	RPM 1140	FLA / MOTOR 1.1	VOLTS 280	FZ 90
QTY	HP	RPM	FLA / MOTOR	VOLTS	HZ PH
QTY	HP	RPM	FLA / MOTOR	VOLTS	HZ PH
DESIGN PRESS 250 PSIG		REFRIGERANT R-717		COIL VOLUME 3.85 CU FT	
<input type="checkbox"/> 13711 Freeway Drive Santa Fe Springs, CA 90670 PH: (562) 921-4310 FAX: (562) 921-6412		<input checked="" type="checkbox"/> 3820 Highway 26 Polo, IL 61064 PH: (815) 946-2351 FAX: (815) 946-3400		<input type="checkbox"/> 1590 Dutch Road Dixon, IL 61021 PH: (815) 946-2351 FAX: (815) 946-3400	
				FAN ROTATION <input type="checkbox"/> CW <input checked="" type="checkbox"/> CCW	

102982