

Cherry Burrell Chemetron Votator Scraped Surface Heat Exchanger- 6 x 72

Mfg: Cherry Burrell

Model:

Stock No. DFPC470.18a

Serial No.:

Cherry-Burrell Chemetron Votator Scraped Surface Heat Exchanger- 6 x 72. Surface area is 9.0 ft. Designed for up to: 400 PSIG @ 375 °F product side and 150 PSIG @ 375 °F jacket side. Motor, 15 hp, 1180 rpm, 413 rpm (final), 230/460 V, 60 Hz, 3 phase. Votator scraped surface heat exchangers can process virtually any pumpable fluid or slurry: they can cook, heat, cool, slush freeze, pasteurize, sterilize, aerate, mix, extrude, crystallize, gel, plasticize, emulsify, or polymerize. The design consists of a concentric shaft with (24) standard 6 in. L x 1-1/2 in. W floating blades. Partlow controller. Inlets: (2) 2 in. S-Line fitting (product), (2) 2 in. threaded port (male, media). Outlets: (2) 1-1/2 S-Line fittings (product), (2) 2 in. threaded port (male, media). Overall dimensions: 9 in. L x 48-1/2 in. W x 68 in. H.





