

Frigid Coil/Imeco Evaporator Unit- 7.66 Ton

Mfg: Frigid Coil/Imeco

Model: USB 35S-363H

Stock No. DPF1678.a

Serial No. 16574-1 RH1

Frigid Coil/Imeco Evaporator Unit- 7.66 Ton. Model: USB 35S-363H. S/N: 16574-1 RH1. Refrigerant: NH3. Max pressure: 250 psig. Orifice feed: 2.05 gpm liquid @ 5.00 psi minimum liquid feed pressure required above coil suction pressure at liquid inlet. Hot gas defrost. Room temperature: 32 °F. Coil temperature: 20 °F. Liquid temperature: 20 °F. Airflow: 13,132 cfm. Galvanized casing. Pan section is hot dip galvanized after fabrication. (3) Reliance Electric Fan Motors, 1/3 hp, 1140 rpm, 120/240 V, 60 Hz, 3 phase. Inlets: (1) 3/4 in. dia. pipe, (1) 1-1/2 in. dia. pipe. Outlets: (1) 3/4 in. dia. pipe, (1) 1/2 in. dia. NPT (female). Overall dimensions: 11 ft. 8 in. L x 40 in. W x 50 in. H.

