

Hot Water Set

Mfg:

Model:

Stock No: DLEC017.38

Serial No:

Hot Water Set. R.L. Deppman Centrifugal Pump. Model: 80-1.5x9.5-9BF. S/N: RLD2086D40. Capacity: 45 gpm. Motor, 3 hp, 1745 rpm, 208-230/460 V, 8.80-8.40/4.20 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2 in. dia. flanged port. Solution tank-8 gallons. Straight wall dimensions: 11-1/2 in. dia. x 17-1/2 in. L. Lagrange Products Shell & Tube Heat Exchanger. Model: 0564-2043. S/N: 226466. Customer No.6235225. MAWP: 150 psi @ 400°F. MDMT: -20°F @ 150 psi. Number of tubes: 17. Tube dimensions: 1/2 in. dia. x 5 ft. 2-1/2 in. L. Heat transfer surface area: approx. 11 sq. ft. Capacity: 0.90 gallons. Inlets: (1) 1-1/2 in. dia. ACME fittings, (1) 1-1/2 in. dia. ACME fittings (steam). Outlets: (1) 1-1/2 in. dia. ACME fittings, (1) 1 in. dia. NPT fittings (steam). (6) Worcester Pnematic Acutator. Model: 2040. S/N: 6C0229. MAWP: 120 psi. Output torque: 265 lb-in. @ 60 psi. Flowserve Vogt Valve. Inlets/outlets: (2) 1 in. dia. NPT fittings. Kunkle Valve Diverter. Model: 910BDCM06AJE. Size: 1/2 in. Capacity: 40 gpm. MAWP: 135 psig. Inlets: (1) 1 in. dia. port (steam), (1) 1 in. dia. port (chilled water), (1) 1 in. dia. port (condensate). Outlets: (1) 1 in. dia. port (steam), (1) 1 in. dia. port (chilled water), (1) 1 in. dia. port (condensate). Overall dimensions: 7 ft. 10 in. L x 4 ft. 7 in. W x 8 ft. H.









