

S-Shaped Stainless Steel Frame Transfer/Accumulation Conveyor

Mfg:

Model:

Stock No: DSBI123.2a

Serial No: 600-016

S-Shaped Stainless Steel Frame Transfer/Accumulation Conveyor. S/N: 600-016. Height at conveyor inlet/outlet: 32 in. H. Conveyor uses a 24 ft. L x 31 in. W. Intralox plastic link belt. AC Tech Intelligent drive control with touchpad controls and digital display. Baldor Industrial Motor: 2 hp, 1725 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. Sumitomo SM-Cyclo Motor Drive: 25 ratio, 1750 rpm (input), 69 rpm (output), 2380 in-lb. torque. Overall dimensions: 23 ft. 6 in. L x 72 in. W x 61 in. H.

