

Loma Cintex Auto II Metal Detector with Conveyor

Mfg: Loma Cintex

Model: Auto II

Stock No: DNBA006

Serial No: 8918

Loma Cintex Auto II Metal Detector with Conveyor. Model: Auto II. Model (conveyor): CS2072. Belt width: 1 ft. 10 in. W. Maximum aperture/clearance above belt: 1 ft. 10 in. W x 3-3/8 in. H. Conveyor infeed/exit height: 3 ft. 3 in. Features a reject mechanism, dimensions: 1 ft. 6 in. W x 6-1/2 in. H. Sensitivity capacities: 1.5 mm ferrous, 1.5 mm non ferrous, 2.0 mm 316 stainless steel. Power supply: 110 V, 50 VA, 50/60 Hz. Baldor industrial motor, 1/5 hp, 1725 rpm, 230/460 V, 1.6/.8 amps, 60 Hz, 3 phase. Speed reducer. Overall dimensions: 8 ft. 2 in. L x 3 ft. 10 in. W x 3 ft. 11 in. H.





