

Stainless Steel COP Tank-300 Gallon

Mfg:



Model:

Stock No.: DNBA026

Serial No.:

Stainless Steel COP Tank-300 Gallon. Inside straight-wall dimensions: 12 ft. 2 in. L x 2 ft. 1 in. W x 1 ft. 9-1/2 in. H. (36) 1/2 in. dia. spray ports. Sanitary Centrifugal Pump. Model: 3 x 2-1/2 DCH2. S/N: CC-17552-1-2. Impeller diameter: 6-1/2 in. Baldor Industrial Motor, 15 hp, 3500 rpm, 230/460 V, 37/18.5 amps, 60 Hz, 3 phase. Inlets: (2) 2 in. dia. S-line fittings (media), (1) 12 ft. 2 in. L x 2 ft. W. (top infeed). Outlets: (1) 2 in. dia. S-line fittings, (1) 3 in. dia. S-line fittings. Overall dimensions: 12 ft. 5 in. L x 2 ft. 6 in. W x 3 ft. 6 in. H.





BALDOR
INDUSTRIAL MOTOR

SERIAL NUMBER	
FRANK	1111111111
HP	1/2
VOLTS	230/460
AMPS	5.7/2.8
R.P.M.	3500
HZ	60
SER. F.	1.15
NEMA NOM. EFF.	86.5%
P.F.	92%
RATING	40C ANB-COAT

BALDOR ELECTRIC CO.
FT. SMITH, ARK.
MFD. IN U.S.A.

BALDOR
INDUSTRIAL MOTOR

SERIAL NUMBER	
FRANK	1111111111
HP	1/2
VOLTS	230/460
AMPS	5.7/2.8
R.P.M.	3500
HZ	60
SER. F.	1.15
NEMA NOM. EFF.	86.5%
P.F.	92%
RATING	40C ANB-COAT

BALDOR ELECTRIC CO.
FT. SMITH, ARK.
MFD. IN U.S.A.

