

Crane Deming Centrifugal Pump

Mfg: Crane Deming

Model: 4066 00001201

Stock No. DTTC2021.

Serial No. DC-860079

Crane Deming Centrifugal Pump. Model: 4066 00001201. S/N: DC-860079. Size: 8 x 8 x 12. Capacity: 1500 gpm. Impeller diameter: 10 in. Westinghouse Motor, 50 hp, 1760 rpm, 175psig, 230/460 V, 124/62 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 8 in. dia. flanged ports. Crane Deming centrifugal pumps are frame mounted with back, pull-out designs and semi-open impellers. Applications include: water, abrasive liquids, acids and oils with uses in a variety of industrial services to include: irrigation, pollution control and cooling towers. Overall dimensions: 5 ft. L x 3 ft. W x 2 ft. 2 in. H.



