

2000 Texwrap Continuous Motion Side Sealer

Mfg: Texwrap Packaging Systems

Model: 2201SS

Stock No.: DNBA071

Serial No.: S1066

2000 Texwrap Continuous Motion Horizontal Side Sealer. Model: 2201SS. S/N:S1066. Maximum film speed: 100 ft/min. Air supply: 80 psi. Air flow: 4 cfm. Belt width No.1: 1 ft. 5-1/2 in., belt width No.2: 1 ft. 3 in., belt width No. 3: 1 ft. 9-1/2 in. Maximum aperture/clearance above belt: 1 ft. 8 in. W x 3 in. H. Infeed/exit height: 2 ft. 11 in. Power supply: 115 V, 15 amps, single phase. Control power supply: 24 VDC. Digital display: 6 in. Roller No.1: 4 ft. 9 in. L x 2 in. dia., roller No.2: 2 ft. 6 in. L x 3-1/2 in. dia., roller No.3: 2 ft. 4-1/2 in. L x 1-1/4 in. dia., roller No.4: 6 in. L x 1-1/2 in. dia. (4) Text Wrap electric motors, 1/7 hp, 2500 rpm, 125 rpm (final), 90 VDC, 1.4 amps, 1 phase, ratio: 20. Baldor electric motor, 1/3 hp, 1750 rpm, 116 rpm (final), 90 VDC, 32 amps, ratio 15. Overall dimensions: 12 ft. L x 4 in. L x 6 ft. 4 in. W x 4 ft. 11 in. H.(ACN710).









