

2001 Bell & Gossett Shell & Tube Heat Exchanger

Mfg: Bell & Gossett

Model:

Stock No: DTTC2074


Serial No: 782912-01

2001 Bell & Gossett Shell & Tube Heat Exchanger. S/N: 782912-01. Part No: BY526200080600. Carbon steel construction. (330) 5/8 in. dia. x 3 ft. 6 in. L multi-tubes. Heat transfer surface area: approx. 185 sq. ft. Coil volume: 18 gal. Shell side MAWP: 150 psi @ 375°F, MDMT: -20°F @ 150 psi. Tube side MAWP: 150 psi @ 375°F, MDMT: -20°F @ 150 psi. Inlets: (1) 13 in. dia. flanged port (product), (1) 10 in. dia. flanged port (media). Outlets: (1) 13 in. dia. flanged port (product), (1) 4 in. dia. flanged port (media). Overall dimensions: 5 ft. 11 in. L x 4 ft. W x 2 ft. H.









NAT'L. BD. 815	
CERTIFIED ITT Industries BUFFALO, NY USA	
BELL & GOSSETT	
SHELL	MAWP 150 PSI at 375 °F
SIDE	MDMT -20 °F at 150 PSI
TUBE	MAWP 150 PSI at 375 °F
SIDE	MDMT -20 °F at 150 PSI
S/N	782312-01
YEAR BUILT	2001
PART NO.	8BY5262000 213211
QSU	203-2
	5-262-20-036-015

NAT'L. BD. 815	
CERTIFIED ITT Industries BUFFALO, NY USA	
BELL & GOSSETT	
SHELL	MAWP 150 PSI at 375 °F
SIDE	MDMT -20 °F at 150 PSI
TUBE	MAWP 150 PSI at 375 °F
SIDE	MDMT -20 °F at 150 PSI
S/N	782312-01
YEAR BUILT	2001
PART NO.	8BY5262000 213211
QSU	203-2
	5-262-20-036-015

SIDE	MDMT -20 °F at 150 PSI
TUBE	MAWP 150 PSI at 375 °F
SIDE	MDMT -20 °F at 150 PSI
S/N	782312-01
YEAR BUILT	2001
PART NO.	8BY5262000 213211
QSU	203-2
	5-262-20-036-015