

Sumitomo SM-Cyclo Inline Drive

Mfg: Sumitomo

Model: CHHJ-1195DBY-258

Stock No. DTTC2102.

Serial No. VA0076411

Sumitomo SM-Cyclo Inline Drive. Model: CHHJ-1195DBY-258. S/N: VA0076411. Input: 7.9 hp/1730 rpm, Output torque: 62500 in.-lb. Ratio: 258. Shaft diameter: 3-9/16 in. Number of sprockets: 2. Sprocket diameter: 1 ft. Number of teeth: 36. Pitch: 1 in. Baldor Electric Motor, 5 hp, 1750 rpm, 208-230/460 V, 13.8-13.4/6.7 amps, 60 Hz, 3 phase. Overall dimensions: 3 ft. 8 in. L x 1 ft. 8-1/2 in. W x 1 ft. 5-1/2 in. H.



