Hot Water Wash Tank-10 Gallon with Conveyor	
Mfg:	Model:
Stock No. DPFI217B.2a	Serial No.

Hot Water Wash Tank-10 Gallon with Conveyor. Belt width 12 in. Effective belt length: 15 in. L. Maximum aperture/clearance: 12 in. W x 11 in. H. Table is equipped with floater and strainer baskets. Centrifugal Pump with Baldor Motor, 1/2 hp, 3450 rpm, 208/230/460 V, 1.9-1.8/.9 amps. Inlets: (1) 1/2 in. dia. male ferrule. Outlets: (1) 1 in. dia. (tank). Overall dimensions: 46-1/2 in. L x 19-1/2 in. W x 38-1/2 in. H. Industrial control panel, Model: 072G-031 CRYOVAC, S/N: 981011221901, electrical requirements: 460 V, 60 Hz, 3 phase. Sumitomo SM Cyclo Motor, 1/2 hp, 1730 rpm, 230/460 V, 1.1 amps, 60 Hz, 3 phase. Sumitomo SM Cyclo Motor Drive, 15 ratio, 117 rpm (final).



















