

Mycom 250SG-MX Screw Compressor Package - 575 HP

Mfg: FES Mycom

Model: 250SG-MX

Stock No.: DTTC815

Serial No.: 2552783

Mycom 250SG-MX Screw Compressor Package. Model: 250SG-MX. S/N: 2552783. Last used with R-717 producing 398.2 tons at 464.3 bhp. Brake hp per ton: 1.165. Vi rating: 3.8. Displacement: 1,110 cfm. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Suction pressure: 33 PSI @ 20°F. Discharge pressure: 180 psi @ 95 °F. Mycom oil separator, Nat'l Bd: 20551, MAWP: 250 psi @ 650 °F. General Electric motor, 575 hp, 3575 rpm, 2400/4160 V, 102/62 amps, 60 Hz, 3 phase. Viking rotary pump, Model: AK 4195, S/N: 11370755. Baldor Super-E motor, 5 hp, 1160 amps, 230/460 V, 16/8 amps, 60 Hz, 3 phase. Mycom Mypro-M controller, 460 V. Overall dimensions: 12 ft. 11 in. L x 4 ft. 10 in. W x 8 ft. 4 in. H. Compressor run time: 63,719.(ACN845).





