

Frigid Coil Evaporator Unit- 10.4 Ton

Mfg: Frigid Coil

Model: SCS-364XH-D-LB-HS-E-R

Stock No. DPFI675B.a

Serial No. 31355-100

Frigid Coil Evaporator Unit- 10.4 Ton. Model: SCS-364XH-D-LB-HS-E-R. S/N: 31355-100. Refrigerant: R-717. Max pressure: 250 psig. Approximate surface area: 113 cu. ft. (3) Centruy AC Fan Motors, 1/2 hp, 60/50 Hz, 1140/1950 rpm, 230 V, 2.2 FLA. Inlets: (1) 3/4 in. dia. pipe, (1) 1-1/2 in. dia. pipe. Outlets: (1) 3/4 in. dia. pipe, (1) 1/2 in. dia. NPT (female). Overall dimensions: 11 ft. 8 in. L x 40 in. W x 50 in. H.

