

Vilter 4416 16-Cylinder Reciprocating Compressor

Mfg: Vilter

Model: 4416

Stock No: DTTC841

Serial No:

Vilter 4416 16-Cylinder Reciprocating Compressor. Model: 4416. Refrigerant: last used with R-717 (ammonia). Nominal capacity: 186 tons at 203.5 bhp with a 96.2°F condensing temperature and a 20°F suction temperature. Displacement: 619 cfm. Max speed: 1,200 rpm. Liquid-cooled heads. Pressure relief valve, Type: 803 TH, inlet: 1/2 in., set pressure: 250 psig, capacity (air): 487 scfm. Inlets: (1) 1-1/2 in. dia. liquid port, (1) 6 in. dia. refrigerant suction port. Outlet: (1) 1 in. dia. NPT (liquid), (2) 3 in. dia. refrigerant discharge ports. Approximate weight: 5,800 lbs. Overall dimensions: 6 ft. 7 in. L x 3 ft. 6 in. W x 6 ft. 3 in. H. (ACN387a).



