

Sullair Rotary Screw Air Compressor

Mfg: Sullair

Model: LS20S-125H

Stock No. DTWA090.31

Serial No. 033-140422

Sullair Rotary Screw Air Compressor. Model: LS20S-125H. S/N: 033-140422. Air pressure rated maximum: 115/125 psi. Screw compressor, S/N: 066-99006291. Toshiba Premium Efficiency Motor, 125 hp, 1775 rpm, 230/460 V, 282/141 amps, 50 & 60 Hz. Oil tank capacity: 40 gallon, MAWP: 200 psi at 250 °F, MDMT: -20 °F at 200 psi., shell thickness: 0.156 in., head thickness: 0.119 in. Evaporator dimensions: 38 in. L x 39 in. W. Premium Fan Motor, 5 hp, 1165 rpm, 230/460 V, 13.4/6.7 amps, 60 Hz, 3 phase. Operates with micro-processor, and digital controller, emergency stop switch. Inlets: (1) 38 in. L x 38 in. W. Outlets: (2) 2 in. dia. NPT (male). Overall dimensions: 101 in. L x 60 in. W x 72 in. H.





