

Stainless Steel Dolly Parton Wash Tank with Stainless Chain Conveyor

Mfg:

Model:

Stock No: DWKN01

Serial No:

Stainless Steel Wash Tank with Honeycomb Flat Wire Chain Conveyor. Number of roller drums: 5. Drum dimensions: 1 ft. 3 in. dia. x 3 ft. 1 in. L. Push rods: 3/4 in. dia. x 6 in. H. Chain width: 3 ft. Gap between links: 3/4 in. Thickness of flat wire: 0.70 in. Rod diameter: 0.195 in. Pitch: 0.6 in. Cleat height: 1-1/2 in. (2) 1 ft. 4 in. L x 11 in. H. access doors. Baldor Electric Motor, 3 hp, 1750 rpm, 208-230/460 V, 8.5-8.2/4.1 amps, 60 Hz, 3 phase. Dodge Speed Reducer, ratio: 14.0, rpm in/out: 1750/125, torque: 4871 in/lbs. Stairway with platform, dimensions: 12 ft. 2 in. L x 2 ft. 1/2 in. W, distance from ground: 5 ft. 4-1/2 in. H. Inlets: (1) 2 ft. 10-1/2 in. L x 2 ft. W product infeed, (1) 2 in. dia. water infeed port. Outlets: (1) 6 in. dia. overflow port, (2) 4 in. dia. drain ports. Overall dimensions: 20 ft. L x 7 ft. 2 in. W x 11 ft. H.









