

Carbon Steel Glycol Cold Well Tank - 500 Gallon

Mfg:	Model:
Stock No. DPPE3001.	Serial No.:

Carbon Steel Glycol Cold Well Tank-500 Gallon. Ingersoll-Dresser Centrifugal Pump, Model: D824, S/N: 873064, Size: 3x2x6. Baldor Electric Motor, 10 hp, 3450 rpm, 208-230/460 V, 26.5-24/12 amps, 60 Hz, 3 phase. Inlets: (2) 6 in. dia. ports, (1) 3 in. dia. port, (1) 1 in. dia. S-Line, (1) 4 in. dia. S-Line. Outlets: (2) 1-1/4 in. dia. ports, (1) 4 in. dia. 150lb ANSI flange. Inside straight wall dimensions: 3 ft. 5 in. dia. x 7 ft. 6 in. H. Overall dimensions: 5 ft. 7-1/2 in. L x 3 ft. 7 in. W x 8 ft. 9 in. H.



