

Ingersoll - Dresser Centrifugal Pump

Mfg: Ingersoll - Dresser

Model: D824

Stock No.: DTTC2047

Serial No.: W0854

Ingersoll - Dresser Centrifugal Pump. Model: D824. S/N: W0854. Size: 3x1.5x8. Impeller diameter: 7 in. Maximum impeller size: 8 in. Pump mat'l: Cl. Baldor Industrial Motor, 10 hp, 3450 rpm, 208-230/460 V, 26.5-24/12 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. flanged port. Outlets: (1) 1-1/2 in. dia. flanged port. Overall dimensions: 2 ft. 1 in. L x 1 ft. 6 in. W x 1 ft. 7 in. H.







