

## D&F Poultry Ice Hopper and Auger

Mfg: D&F

Model:

Stock No: EKTF7260.2

Serial No:

D&F Poultry Ice Hopper and Auger. Baldor motor, 1 hp, 1725 rpm, 208-230/460 V, 3.6-3.4/1.7 amps, 60 Hz, 3 phase. Flexaline motor drive, 60 ratio, maximum input: 0.9 hp, rating: 1750 rpm, output: 28.75 rpm. Stainless steel body. Container capacity: 120 gallon. (3) Screws: 6 in. diameter x 47 in. L. Inlet: 20 in. L x 20 in. W. Outlet: 14 in. L x 12 in. W. Overall dimensions: 81 in. L x 29 in. W x 58 in. H. (ACN85)



