

RVS Ammonia Accumulator Package

Mfg: RVS

Model:

Stock No.: DTTC2058B

Serial No.: 89580 / 89590

RVS Ammonia Accumulator Package. RVS recirculator tank: S/N: 89580. Nat'l. Bd: 2382. Dimensions: 9 ft. Dia. x 19 ft. 10 in. L. Inside straight-wall dimensions: 8 ft. 4 in. dia. x 15 ft. L. Original MAWP: 150 psi @ -20°F to 300°F. MDMT: 60 psi @ -40°F. Recertified by Fru-Con in 2004 with MAWP: 60psi @ -60°F. Nat'l Bd: 1173. Hydro test: 225 psi. Inlets/outlets: (1) 3/4 in. dia. FNPT, (1) 1 in. dia. port, (1) 1-1/2 in. dia. port, (1) 2 in. dia. port, (2) 14 in. dia. ports. Refrigerant Valves & Systems accumulator tank: S/N: 89590. Nat'l Bd: 2342. Straight-wall dimensions: 2 ft. 7 in. dia. x 5 ft. 8 in. L. MAWP: 250 psi @ 300 °F. MDMT: -20 °F @ 250 psi. Recertified by Fru-Con Construction Corp., Nat'l Bd: 1173, Date altered: 9/2004, MAWP: 100 psi @ -60°F. (2) Cyrus Shank safety relief valves: type: 804, capacity: 880 scfm. Refrigerating Specialties Inc. pressure regulator: type: A2BK, Ref. No: G07598, range: D 5-20 kg/cm² (75/280 psig). Inlets: (1) 2 in. dia. port, (1) 3/4 in. dia. port, (1) 1/2 in. dia. port, (1) 1-1/2 in. dia. port. Outlets: (1) 3/4 in. dia. port, (1) 4 in. dia. flanged fitting, (1) 1-1/2 in. dia. port, (1) 1-1/2 in. dia. flanged fitting, (2) 2 in. dia. flanged fittings. Henry Technologies oil pot- 10 Gallon. Model: RA-10034-600. Nat'l Bd: 14668. Inside straight-wall dimensions: 10 in. dia. x 2 ft. 6 in. L. MAWP: 300 psi @ 300 °F. MDMT: -55/-60 °F @ 300/100 psi. (2) Cyrus Shank safety relief valves, Type: 803, max pressure: 250 psig/573 scfm. Inlets: (1) 2 in. dia. flanged port, (1) 3/4 in. dia. port. Outlets: (1) 1/2 in. dia. port, (1) 1 in. dia. FNPT. Overall dimensions: 20 ft. L x 8 ft. 4 in. W x 17 ft. H.













