

1990 Precision Heat Exchanger Shell and Tube Chiller with Surge Drum


Mfg: Precision Heat Exchanger Co.


Model:

Stock No. DTTC2098.

Serial No. 11856-6

1990 Precision Heat Exchanger Co. Shell and Tube Chiller with Surge Drum. S/N: 11856-6. Nat'l Bd: 5259. Refrigerant: ammonia. MAWP shell side: 150 psi @ 200 °F MDMT: -20 °F @ 150 psi. MAWP tube side: 100 psi @ 200 °F. MDMT tube side: -20 °F @ 100 psi. 1993 Refrigeration Valves Surge Drum, S/N: 93451, Nat'l Bd: 5794, MAWP shell side: 150 psi @ 200 °F, MDMT shell side: -20 °F @ 150 psi, (1) Parker float switch. Liquid level probe. Inlets: (1) 4 in. dia. flanged fitting, (1) 3 in. dia. port. Outlets: (1) 4 in. dia. flanged fitting, (1) 1-1/2 in. dia. port, (1) 1 in. dia. port. Overall dimensions: 26 ft. 4 in. L x 4 ft. 6 in. W x 7 ft. 11 in. H.





Note: the following pictures show the exact unit prior to removal.

