

**2005 GEA / FES 675-GL Rotary Screw Compressor Package – 800 HP**

**Mfg: GEA / FES**

**Model: 675-GL**

**Stock No.: GAMB08.137a**

**Serial No.: 05013018**

GEA / FES Rotary Screw Compressor Package. Model 675GL Swing Compressor. Year: 2005. Item EC-C-8. FES Contract 05013018. Design suction: 33.5 PSIG / +20F. Nominal capacity: 719 TR. Design Discharge: 174.9 PSIG / +93F. Brake HP: 748.2. Includes GEA micro. Refrigerant: ammonia. Removed from operation in January/February 2014. Unit has been stored indoors. Package is equipped with: Thermosyphon Oil Coolers, Shell and Plate style, Oversized Oil Separators, Dual Oil Filters, Motor Temperature and Vibration Sensors, Benshaw motor starter, RAM Industries motor. Compressor specs: model Z-52, serial Z0293, mark 4, year 2005, 406 PSIG, 1953 CFM, R-717. Motor specs: 800 HP, 460V, 882 FLA, 3580 RPM, 3-phase, 60 Hz, 5808S frame. Hours runtime: 27,711. Weight: 18,000 lbs. Overall dimensions: 84 in. W x 180 in. L x 120 in. H.









