

## Clark Forklift

Mfg: Clark

Model: RHY 160 B

Stock No. GEEQ009.

Serial No. HY 1425 D-45-2 156

Clark Forklift (green). Model: RHY 160 B. S/N: HY 1425 D-45-2 156. Capacity: 16,000 lbs @ 24 in. load center. Fork dimensions: 93 in. L x 8 in. W. Fuel: diesel. Detroit Diesel engine, motor stamping: OWC 5125424-145. Oil filter: NAPA Gold bypass 1749. Hydraulic oil filter: NAPA Gold 3122. (2) Front tires: Firestone Super Ground Grip Loader-Dozer, tubeless, nylon 12-ply rated, size: 17.5-25 L-2. (2) Rear tires: Kumho Superlug 323A, tube type, nylon, inflation: 6610 lb @ 115 psi (single)/ 5800 lb @ 105 psi (dual), size: 10.00-20. Overall dimensions: 22 ft. 3 in. L x 94 in. W x 10 ft. 3 in.





