

FES/Mycom Screw Compressor Package-500 hp

Mfg: FES/Mycom

Model: 250LU-M

Stock No. D TTC803.

Serial No. 2511201

FES/Mycom Screw Compressor Package- 500 hp. Model: 250LU-M. S/N: 2511201. Job No: 560-22495. Scew is newly rebuilt and never run since its rebuild. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. E.L. Nickel Co. Oil Separator, Model: C-1525, S/N: 21901, Nat'l Bd: 19930, MAWP: 250 psi. Maximum temperature: 650 °F. Viking Rotary Pump, Model: AL195, S/N: 0992379. Vanguard Motor, 5 hp, 1150 rpm, 203/460 V, 60 Hz, 3 phase. Mycom Mypro-M Controls. New Un-Used Siemens Motor, 500 hp, 3565 rpm, 460 V, 532 amps, 60 Hz, 3 phase. Inlets: (1) 8 in. dia. suction port with a 14-1/2 in. dia. flange. Outlets: (1) 5 in. dia. discharge. Overall dimensions: 13 ft. 1 in. L x 61 in. W x 110 in. H.



