

FES/Mycom Screw Compressor Package-500 HP

Mfg: FES/Mycom

Model: 250SU

Stock No.: DTTC812

Serial No.: 2551183

Mycom 250SU Screw Compressor Package - 500 HP. Model: 250SU. S/N: 2551183. Nat'l Bd: 19939. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Maximum working pressure: 250 psi. Maximum temperature: 650 °F. Minimum temperature: 20 °F. Head radius: LLL 2:1. Head thickness: 5/16 in. Shell thickness: 5/16 in. Displacement: 1,110 cfm. General Electric induction motor, 500 hp, 3575 rpm, 2400/4160 V, 107/62 amps, 60 Hz, 3 phase. Viking rotary pump, Model: AK 4195, S/N: 11073752. Baldor Super-E motor, 5 hp, 1180 rpm, 230/460 V, 18/8 amps, 60 Hz, 3 phase. Mypro-M Mycom controller. Outlets: (1) 4 in. dia. port. Overall dimensions: 12 ft. 2 in. L x 4 ft. 8 in W x 7 ft. 8 in. H. (SR450) (ACN845).









