

## Stainless Steel Product Saver

Mfg:

Model:

Stock No. GM-556.8

Serial No.

Stainless Steel Product Saver. Model: N/A. S/N: N/A. Inside dimensions: 27 in. dia. x 45 in. L. 316 stainless steel construction. Equipment comes with a 53 in. L x 32 in. W removable lid and (3) Allen-Bradley limit switches. 12 in. L x 12 in. W front access door allows for easy access to product. Inlets/outlets: (1) 3/4 in. dia. MPT, (1) 1 in. dia. FPT, (1) 3 in. dia. bottom outlet pipe, (1) 23 in. dia. inlet, (1) 18 in. L x 17 in. W chute. 1/2 HP SM-CYCLO Motor, 3-phase. SM-CYCLO motor drive, 219 rpm (output), 8-ratio. Overall dimensions: 90 in. L x 39 in. W x 58 in. H.



