

Sullair Screw Compressor-100 hp

Mfg: Sullair

Model: CB12LAR22-30

Stock No. HBSV003.

Serial No. 056-00939

Sullair Screw Compressor Package- 100 hp. Model: CB12LAR22-30. S/N: 056-00939. Refrigerant: R-22. Max pressure: 250 psig. Compressor run time: 24719 hrs. Sullair Centrifugal Compressor, Model: 5A 266, S/N: 79DH12-0109. Lincoln Motor, 100 hp, 3525 rpm, 230/460 V, 232/116 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. diameter suction pipe. Outlets: (1) 2 in. dia. discharge pipe. Overall dimensions: 96 in. L, 48 in. W, 94 in. H. Package features an oil separator tank with an attached shell and tube heat exchanger. Oil Separator, MAWP @ 250 °F: 300 psi. Basco Type 500 Shell and Tube Heat Exchangers, Model 240707.



