

Fuller Rotary Vane Compressor- 100 HP

Mfg: Fuller

Model: A175

Stock No. DTTC821.

Serial No. 702-0678-103

Fuller Rotary Vane Compressor- 100 HP. Model: A175. S/N: 702-0678-103. Capacity: 99 TR. Speed: 590 rpm. Maximum temperature: 300 °F. Louis-Allis Motor, S/N: 2359174, 100 hp, 1760 rpm, 220 V, 246 amps, 60 Hz, 3 phase. Inlets: (1) 6 in. dia. port, (1) 1-1/2 in. dia. port. Outlets: (1) 8 in. dia. port. Overall dimensions (motor): 41 in. L x 37 in. W x 30 in. H. Overall dimensions (compressor): 68 in. L x 59 in. W x 57-1/2 in. H.



