

## Fuller Rotary Vane Screw Compressor- 60 HP

Mfg: Fuller

Model: A175

Stock No. DTTC822.

Serial No. 702-0679-103

Fuller Rotary Vane Screw Compressor- 60 HP. Model: A175. S/N: 702-0679-103. Capacity: 105 TR. Speed: 590 rpm. Maximum temperature: 300 °F. Motor, S/N: 1400518, 60 hp, 900 rpm, 220/440 V, 115/76.5 amps, 60 Hz, 3 phase. Inlets: (1) 6 in. dia. port, (1) 1-1/2 in. dia. port. Outlets: (1) 8 in. dia. port. Overall dimensions (motor): 40 in. L x 26 in. W x 22 in. H. Overall dimensions (compressor): 68 in. L x 59 in. W x 57-1/2 in. H.



