

Sullair Screw Compressor Package - 100 hp

Mfg: Sullair

Model: CB12LAR22-30

Stock No: HBSV007

Serial No: 056-00941

Sullair Screw Compressor Package. Model: CB12LAR22-30. S/N: 056-00941. Refrigerant: R-717. Max pressure: 250 psig. Sullair centrifugal compressor, model: 5A 266, S/N: 81DH12-0012. Lincoln motor, 100 hp, 3525 rpm, 230/460 V, 232/116 amps, 60 Hz, 3 phase. Package features an oil separator tank with an attached shell and tube heat exchanger. Oil separator, MAWP @ 250 °F: 300 psi. Basco type 500 shell and tube heat exchangers, Model 240707. Inlets: (1) 3 in. diameter suction pipe. Outlets: (1) 2 in. dia. discharge pipe. Overall dimensions: 8 ft. L x 4 ft. W x 7 ft. 10 in. H.

