

## FES 775 / Mycom 320 SU-MX Rotary Screw Compressor Package - 1000 HP

Mfg: FES Mycom

Model: 775 / 320 SU-MX

Stock No: DTTC826

Serial No: 3251373

FES 775 / Mycom 320 SU-MX Rotary Screw Compressor Package. Model: 775 / 320 SU-MX. S/N: 3251373. Contract No: 88-0227-0303-09. Refrigerant: last used with R-717 (ammonia). Mycom rotary screw compressor, Model: 320 SU-MX, S/N: 3251373. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Nominal capacity: 825 tons at 936.2 bhp with a 95°F condensing temperature and a 20°F suction temperature. Displacement: 2,236 cfm. FES Oil Separator, S/N: 88292, National Board: 3603, MAWP: 250 psi at 200 °F, MDMT: 20 °F. Reliance electric motor, 1000 hp, 4160 rpm, 3575 rpm, 119 amps, 60 Hz, 3 phase. FES rotary positive displacement pump, S/N: 11522857, P/N: 290-000050-000. Baldor industrial motor, 10 hp, 1760 rpm, 208-230/460 V, 26.5-28.4/14.2 amps, 60 Hz, 3 phase. FES Micro II control panel. Inlets: (1) 16 in. dia. flanged ammonia port. Outlets: (1) 4 in. dia. port. Approximate shipping weight: 18,600 lbs. Overall dimensions: 16 ft. 6 in. L x 5 ft. 3-1/2 in. W x 8 ft. 8 in. H. Compressor run time: 9,970 hrs since rebuilt by Mycom. (SR450)(ACN1450).











