

2002 Safeline Metal Detector


Mfg: Safeline

Model: PPH/12X05/SS/100-300/HD/V3

Stock No. HDAF607.79

Serial No. 52024

2002 Safeline Metal Detector. Model: PPH/12X05/SS/100-300/HD/V3. S/N: 52024. Ref. No: 18218. M/C No: 333. Ref. Phase: +0.00°. Pwr/Dr No: 313. Ref. Phase: +0.00°. Pwr/Dr No: 063. OOBV: 80 mV. Maximum aperture/clearance above belt: 12 in. W x 3-1/2 in. H. Belt width: 9 in. Unit features an Intralox belt and pneumatic, solenoid-activated reject mechanism. Leeson Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.6/0.8 amps, 60 Hz, 3 phase. Textron Power Transmission, ratio: 25, 69 rpm (final). Conveyor infeed/exit height: 35-1/2 in. Overall dimensions: 13 ft. 11 in. L x 79 in. W x 44 in. H. (ACN250).





Metal Detector Specifications

Model PPH/12x05/SS/100-300/H0/V3

S/N: 52024 Ref. No.: 18218

M/C#: 333 Ref. Phase +0.00°

PWR/DR#: 052 OOBV: 30.mV

M/C#: 313 Ref. Phase +0.00°

PWR/DR#: 003 OOBV: 80.mV

Safeline Inc
Tampa, Florida



