

Amsco Portable Packaging Machinery Line Bag Sealer

Mfg: Amsco

Model: 175H

Stock No. DTWA342A.4

Serial No. 981

Amsco Portable Packaging Machinery Line Bag Sealer. Model: 175H. S/N: 981. Belt width: 15 in. Maximum aperture/clearance above belt: 2 in. W x 15 in. H. Height and width adjustable conveyors. Electrical requirements: 115 V, 15 amps, 60 Hz, single phase. Baldor Industrial Motor, 1/2 hp, 1725 rpm, 115/230 V, 7.4/3.7 amps, 60 Hz, single phase. Reeves Variable Speed Drive. Infeed/exit height: 28 in. Overall dimensions: 10 ft. 2 in. L x 44 in. W x 51 in. H. AshlandElectrical Products Centrifugal Blower, Model: C13S24Q-1CC, S/N: 134. Bodine Electrical Company Motor, 1/6 hp, 3450 rpm, 115 V, 60 Hz, single phase.





