

## Table Top Conveyor with Adjustable Legs

Mfg:

Model:

Stock No. DTWA353F.

Serial No.:

Table Top Conveyor with Adjustable Legs. 6 in. conveyor chain with a 4-1/2 in. Max product width. Infeed/Outfeed height: 33-1/2 in. Baldor Motor: 1/2 hp, 1750 rpm, 180V, 2.9 amps, 3 ph. Winsmith Drive: 10 Ratio, 175 Final rpm, 617 in./lb. torque. Overall Dimensions: 128 in. L x 20 in. W x 49 in. H.

