

Kewanee Forced Draft Steam Boiler- 80 HP

Mfg: Kewanee

Model: KF1.5-762-H0

Stock No. HDCD370.33a

Serial No. P8126

Kewanee Forced Draft Steam Boiler- 80 HP. Model: KF1.5-762-H0. S/N: P8126. Type: KF. Order: 432912-B. Catalog: H3S580-KG0. Forced draft oil-gas boiler in good, clean condition. MAWP steam: 150 lb. Heating surface area: 400 sq. ft. Maximum firing range: 3348 MBh. Valve capacity: 3200 lbs/hr. Firing range (gas): 1700-3400 MBh. Firing range oil: 12.0-24 gph. Gas Type and Pressure: NAT.281NWC. Gas Oil Burner No: R310504. Rating: 2678 MBh. Blower specification: 1.5 hp, 460 V, 3.0 amps, 60 Hz, 3 phase. Control requirements: 115 V, 60 cycles, single phase. Inlets: (1) 1/2 in. dia. NPT (male, prime), (1) 1 in. dia. NPT (male, water feed), (1) 1 in. dia. NPT (female, low water cut-off), (1) 1-1/2 in. dia. NPT (female, gas-oil). Outlets: (1) 1-1/2 in. dia. (female, evacuate), (1) 2-1/2 in. dia. pressure relief, (1) 6 in. dia. port (steam), (1) 11 in. dia. (exhaust gas). Overall dimensions: 12 ft. 4 in. L x 55-1/2 in. W x 100 in.

H.



